



20-30 HP FIXED SPEED ROTARY SCREW COMPRESSORS

## L-Series

### Advanced Technology. Inspired Simplicity.

L-Series compressors from Gardner Denver feature more than just the latest compressor technology. They contain the cleanest, simplest, most intuitive machine layouts on the market. Equipped with standard TEFC main motors, wye-delta starters, GD Governor™ microprocessor controllers and quiet enclosures, an L-Series unit from Gardner Denver is the optimal solution when a feature-rich, simple-to-operate compressor is required.

### First Class Serviceability

The L-Series units set a new standard in serviceability. By utilizing integrated airoend design techniques, Gardner Denver delivers unprecedented access to service items such as; a high efficiency air filter, air/oil separator and oil filter. At the same time, the compact design eliminates unneeded connections and minimizes piping; reducing the opportunity for leaks. Couple these features with standard automatic belt tensioning and you have a world class small horsepower compressor package.

### Configuration Flexibility

L-Series compressors are available in base mount or AirStation™ configurations. The plug-and-play AirStation™ configuration is an L-Series compressor mounted on a horizontal receiver tank with or without a refrigerated air dryer. Featuring standard high-end components such as a three-way bypass valve, stainless steel piping, integrated fork lift slots and an optional electric tank drain, the L-Series AirStation™ is the ideal solution for a compressed air system that requires minimal installation time and cost.

**Gardner**  
**Denver**®

## L15-L22 ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR		60 Hz				NOISE LEVEL <sup>2</sup>	WEIGHT		DIMENSIONS L x W x H
	HP	KW	NOMINAL PRESSURE		FAD <sup>1</sup>			DB(A)	LBS	
			PSIG	BAR	ACFM	M <sup>3</sup> /MIN				IN. (MM)
L15	20	15	110	7.6	87.2	2.47	73			
			130	9.0	80.8	2.29				
			190	13.1	60.7	1.72				
L18	25	18	110	7.6	110.2	3.12	74	857	389	32 x 35 x 50 (881 x 820 x 1274)
			130	9.0	103.0	2.92				
			190	13.1	79.6	2.25				
L22	30	22	110	7.6	125.7	3.56				
			130	9.0	117.2	3.2				
			190	13.1	92.3	2.61				

1) Data measured and stated in accordance with ISO1217, Ed. 4, Annex C & Annex E at the following conditions:

Air Intake Pressure 1 bar A, Air Intake Temperature 20° C, Humidity 0% (Dry).

2) Noise levels are for air-cooled models and measured in free field conditions in accordance with ISO 2151, tolerance +/- 3 dB.

## AIR STATION SPECIFICATIONS, 60 HZ

MODEL	DRYER MODEL	RECEIVER SIZE GAL. (LITERS)	REFRIGERANT	WEIGHT LBS (KG)		DIMENSIONS L x W x H IN. (MM)	
				120 GAL	240 GAL	120 GAL	240 GAL
L15	XGNC	120, 240 (454, 908)	R134A	less dryer 1298 (589)		less dryer 75 x 35 x 76 (1905 x 889 x 1938)	
L18				with dryer 1701 (772)		with dryer 75 x 35 x 76 (1905 x 889 x 1938)	
L22							

Dryer on AirStation™ package has separate electrical connection and voltage.

## L-Series Features (20-30 HP)

- Belt drive, oil flooded, single stage rotary screw air compressor
- AEON 4000 lubricant
- Air-cooled only
- Optional automatic zero-loss condensate drain (with receiver tank selection)
- CRN and ASME rated aftercooler
- GD Governor™ microprocessor controller
- Integrated spin-on oil filter, spin-on air/oil separator and two-stage air filter
- Integrated thermostatic thermal mixing valve
- NEMA 1 electrical enclosure, NEMA 4 optional
- Load/no load control and timed shutdown
- Moisture separator (shipped loose)
- Mounted and wired wye-delta starter
- Optional ASME receiver tank (120, 240 gallons)
- Optional mounted non-cycling refrigerated dryer (with receiver tank selection)
- Optional sequencing kit
- Quiet enclosure
- TEFC main motor
- Standard manual tank drain (with receiver tank)
- Second pressure band control for lead/lag operation
- Stainless steel piping (with receiver tank and mounted dryer)
- Optional inlet modulation
- UL labeled electronics (including C-UL-US open industrial control panel)
- Voltage: 200T/230T/380/400/460T/575V

**Gardner  
Denver®**

1800 Gardner Expressway  
Quincy, IL 62305  
[www.gardnerdenver.com](http://www.gardnerdenver.com)



©2024 Industrial Technologies and Services, LLC  
Printed in U.S.A.  
GSCS-L15-L22 1st Ed. 6/24  
Supersedes GSCS-L07-L22 4th Ed. 3/21

Please recycle after use.