

COMPRESSOR DATA SHEET



In Accordance With Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer: Gardner Denver		
2	Model Number: L18RS-25hp-130psi		Date: 08/28/23
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled		Type: Screw
			# of Stages: 1
3*	Full Load Operating Pressure ^b	130	psig ^b
4	Drive Motor Nominal Rating	25	hp
5	Drive Motor Nominal Efficiency	91.7	percent
6	Fan Motor Nominal Rating (if applicable)	NA	hp
7	Fan Motor Nominal Efficiency	NA	percent
8*	Input Power (kW)	Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	22.03	95.0	23.19
	19.76	85.0	23.23
	17.56	75.0	23.41
	15.43	64.9	23.78
	13.37	54.7	24.44
	11.58	45.5	25.45
9*	Total Package Input Power at Zero Flow ^{c, d}	3.4	kW
10	Isentropic Efficiency	63.23	%
11	<p>Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, +5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</p>		

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator
 Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	Zero Flow Power
m ³ / min	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.1

12/19 Rev 3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.