

Ideal Applications

- Restaurant Grease Traps
- Cesspool Pumping
- Septic Tanks
- Oil Well Service
- Holding Pits
- Sludge Removal

PERFORMANCE DATA

		VACUUM inHG						FREE AIR	PRESSURE PSI			
		24	21	18	15	12	6	0	7.25	14.5	21.75	29
1000	CFM	187	208	222	232	240	245	247	243	232	221	207
	HP	12.1	12.9	13.7	14.5	15.1	16.8	18.1	20.8	24.4	29	33.5
1250	CFM	246	275	296	306	315	324	325	319	306	291	275
	HP	16.1	16.8	17.4	18.1	18.8	20.4	22.5	25.1	30.2	35.8	42.0
1500	CFM	309	353	376	888	400	414	417	400	384	359	333
	HP	18.8	19.8	20.8	21.7	22.5	24.3	26.1	29.2	35.5	42.1	48.9

WEIGHT

	KG	LBS
BARE MACHINE	179	395
WITH RFV & FILTER	189	417

DIMENSIONS

	MILLIMETERS	INCHES
A	862	33.93
B	408	16
C	430	16.9
D	302	11.88
E	649	25.5
F	175	6.88
G	300	11.8

